



L029890509

Navigation LED P28s T29x119mm 230V
76mA 1300Lm 10W 6200-6800K 25.000
hours AC/DC IP65 EMC approved Ship lamp

Marine & Industry, Navigation Led



General		Energy		
Socket	P28s	Operating voltage	230 V	
Bulb shape	T29	Volt	100..240 V	
Diameter	29.00 mm	Frequency	50..60 Hz	
Total length	119.00 mm	Watt	10 W	
Finish	Clear	Current type	AC/DC	
Colour	White Daylight	Power factor	0.5	
Lifespan	25000 hours	Energy consumption	10 W	
Switches	50000	Replacement wattage	88 W	
Beam angle	360 °	Lamp efficacy	130.00	
Dimmable	No	LED		
Degree of protection	IP65	Filament LED	No	
Net weight	0.112 kg	LED type	SMD	
Warranty	2 years	Number of leds / sticks	72	
Light		Adjustable beam angle	No	
Kelvin	6200..6800 K	Ordering details		
Colour temp nr	862..868	L029890509	Quantity pc(s)	EAN
Stable lumen	1300 lm	Single package	1	8718739059627
Initial lumen	1400 lm	Inner carton	10	18718739059624
Color Rendering Index (CRI)	80	Outer carton	100	28718739059621