


Type Type Type	Bestell-Nr. Order No. No. de Cde	Isolation Griffteil Insulation handle Isolation	Temperaturbereich Operating temperature Température	Metalleile / Oberfläche Metal parts / plating Partie métallique / traitement	Bemessungsstrom Rated current Intensité assignée	Steckweite Plug spacing Entraxe
			°C		A	mm

1:1




<b>KB1-2,54/1</b>	<b>24.0053-*</b>	PA	-40...80	Cu(Leg) <sup>1)</sup> Cu(alloy) <sup>1)</sup> Cu(alliage) <sup>1)</sup>	10	2,54
-------------------	------------------	----	----------	-------------------------------------------------------------------------------	----	------

\* Farben / Colours / Couleurs



1:1




<b>KB1-5,08/1</b>	<b>24.0054-*</b>	PA	-40...80	Cu(Leg) <sup>1)</sup> Cu(alloy) <sup>1)</sup> Cu(alliage) <sup>1)</sup>	10	5,08
-------------------	------------------	----	----------	-------------------------------------------------------------------------------	----	------

\* Farben / Colours / Couleurs



1:1



<b>KB2-10</b>	<b>24.0051-*</b>	PA	-40...80	Cu(Leg) <sup>1)</sup> Cu(alloy) <sup>1)</sup> Cu(alliage) <sup>1)</sup>	10	10
---------------	------------------	----	----------	-------------------------------------------------------------------------------	----	----

\* Farben / Colours / Couleurs



<sup>1)</sup> Hartkupferlegierung, vergoldet

<sup>1)</sup> Hard-drawn copper alloy, gold plated

<sup>1)</sup> Alliage de cuivre dur, doré