


| ITEM | PART# | DESCRIPTION | QTY | UOM |
|------|------------|--|-----|-----|
| A, B | 5601230600 | DURACLIK ISL HOUSING 6P | 2 | PC |
| C | 5601250600 | New 2.0 W/B CONN REC. 6 WAY ISL Gray | 2 | PC |
| D | 5601240101 | DURACLIK ISL crimp receptacle terminal | 12 | PC |
| E | -- | PAPER PRINTED PAPER WHITE | 1 | PC |

| FROM | TO | DESCRIPTION | COLOR |
|------|----|-----------------------------------|-------|
| A1 | B6 | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| A2 | B5 | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| A3 | B4 | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| A4 | B3 | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| A5 | B2 | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| A6 | B1 | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |



| TABLE | | | |
|-------------|--------|----------|--------------------------------------|
| PART NUMBER | L1 | L2 (REF) | TITLE |
| 2183221061 | 150±8 | 63 | DURA-CLIK ISL R-R 6CKT 150MM DISC Sn |
| 2183221062 | 300±10 | 138 | DURA-CLIK ISL R-R 6CKT 300MM DISC Sn |
| 2183221063 | 600±10 | 288 | DURA-CLIK ISL R-R 6CKT 600MM DISC Sn |

- NOTES
1. Cable assembly must pass 100% for continuity and polarity.
 2. Connector view shown is from mating side.
 3. Label text must be 2mm max. in height with Arial font.
 4. Label must be wrapped in Flag type on a single cable.

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

| REVISION | | | |
|------------|-----|-----------------|---------|
| DATE | REV | DESCRIPTION | CHANGER |
| 24/05/2021 | A | INITIAL RELEASE | ARAJU |

| | | | | | |
|---|---|---------------------------|----------------------------|--------------------------|-----------------|
| FUNCTIONAL SYMBOLS $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$ DIVISIONAL SYMBOLS | THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION | | CURRENT REV DESC: | | |
| | DIMENSION UNITS | SCALE | EC NO: 665457 | | |
| | mm | NTS | DRWN: ARAJU 2021/05/22 | | |
| | GENERAL TOLERANCES (UNLESS SPECIFIED) | | CHK'D: RDESAI01 2021/05/28 | | |
| ANGULAR TOL ± ° | | APPR: RDESAI01 2021/05/28 | | PRODUCT CUSTOMER DRAWING | |
| 4 PLACES ± | | INITIAL REVISION: | | DOCUMENT NUMBER | DOC TYPE |
| 3 PLACES ± | | DRWN: ARAJU 2021/05/22 | | 2183221061 | PSD |
| 2 PLACES ± | | APPR: RDESAI01 2021/05/28 | | 000 | REVISION |
| 1 PLACE ± | | MATERIAL NUMBER | | 1 | A |
| 0 PLACES ± | | CUSTOMER | | SHEET NUMBER | |
| DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS | | THIRD ANGLE PROJECTION | DRAWING | SERIES | MATERIAL NUMBER |
| | | | A4-SIZE | 218322 | SEE TABLE |
| | | | | | GENERAL MARKET |
| | | | | | 1 OF 1 |

| | | | | |
|-----------------|----|--------------|------------|----------|
| DOCUMENT STATUS | P1 | RELEASE DATE | 2021/05/28 | 13:17:28 |
|-----------------|----|--------------|------------|----------|