



SUHNER® COAXIAL CONNECTOR DATA SHEET

TYPE 43_BNC-50-0-1/133_N

Description

T-adaptor, 2 jacks, 1 plug



General Information

BNC Interface dims acc. to: IEC 60169-8_MIL-STD-348A/301_CECC 22120
Weight: 0.0184 Kg/ 0.65 oz

Electrical Data

Impedance: 50Ω
Interface frequency max.: 4 GHz

Piece Parts

Centre contact:
Outer contact:
Body:
Insulator:
Coupling nut:
Gasket:

Material

Copper Beryllium / Brass
Brass
Brass
PFA / PTFE
Brass
MQ (Silicon Rubber)

Surface Plating


Gold Plating (Nickel underplated)
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Attachments

Catalogue drawing: DCA-00013549

Notes

Order as **43_BNC-50-0-1/133_NE** for Single
Order as **43_BNC-50-0-1/133_NH** for Bulk 100 pcs

<small>WAIVER!</small> While the information contained in this folder has been carefully compiled to the best of our present knowledge, it is not intended as representation or warranty of any kind on our part regarding the fitness of the products concerned for any particular use or purpose and neither shall any statement contained herein be construed as a recommendation to infringe any industrial property rights or as a license to use any such rights. The fitness of each product for any particular purpose must be checked beforehand with our specialists.		 HUBER+SUHNER HUBER+SUHNER AG Interconnect Division CH-9100 Herisau Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 45 90 http://www.hubersuhner.com
Issued: 02.09.04 16:41	Document: DOC-0000194125	
RF_Ad_W_PDF <i>uncontrolled copy</i>	Page 1	