


## CUBE20S COMMUNICATION MODULE

RS232

RS232

[Link to Product](#)

### Illustration



Product may differ from Image

### Approvals



**Internal communication**

Module Supply	via system connection
Current consumption	100 mA

**Technical Data**

Transfer parameters	150 bit/s...115.2 kbit/s
---------------------	--------------------------

**General data**

Protection	IP20
Connection	Spring clamp plug-in terminals: max. 1.5 mm <sup>2</sup> (AWG 16)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

**Diagnostic**

Communication status	via LED
Diagnostic via LED	per module and channel
Diagnostic via BUS	per module
Monitoring - under voltage	yes
Monitoring - no voltage	no
Short circuit and overload	yes

**Commercial data**

country of origin	TH
customs tariff number	85389099
minimum order quantity	1