

M16 MALE, 0° 14 POLE,

PUR 8x0.25 + 2x0,5 black 2m

M16

Male straight

14-pole


12-pole used

Further cable lengths on request.

[Link to Product](#)**Illustration**

P	white
J	green
T	yellow
S	gray
G	pink
R	red
E	black
O	violet
A	brown 0.75 mm ²
M	
L	blue 0.75 mm ²
U	

Male



Product may differ from Image

Form

16751

Technical Data

Operating voltage	24 V AC/DC
Operating current per contact	max. 3 A
Protection	IP67 inserted and tightened (EN 60529)

Cables

Cable number	959
No./diameter of wires	8×0.25 + 2×0.5 mm ²
Jacket Color	black
Material (jacket)	PUR/PVC
Outer diameter	approx. 8.0 mm
Bend radius (moving)	15 × outer Ø
Temperature range (fixed)	-25...+70 °C
Temperature range (mobile)	-5...+70 °C

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1