





**M12 female receptacle X coded front mount solder**

Flange M12 female  
Mounting nut  
X-coded, 8-pole  
straight  
Solder connection  
Front mounting

**[Link to Product](#)****Illustration**

# Female



Product may differ from Image

## Form

21151

## Technical Data

Operating voltage max. 50 V AC/60 V DC

Operating current per contact	max. 0.5 A
Transfer parameters	10 Gbit/s
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

**General data**

Temperature range	-40...+85 °C
-------------------	--------------

**Commercial data**

customs tariff number	85369010
minimum order quantity	1