
Item no.: 261-301
Product description: 2-CONDUCTOR TERMINAL BLOCK FOR SCREW OR
SIMILAR MOUNTING TYPES 3.2 MM Ø MOUNTING ADAPTER
AVAILABLE FOR TS 35 (209-123)



Produkt kann von Bild abweichen / product may differ

Packing unit 200 4*50 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	24 A
Weight	2.316 g
Color	gray
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	18 mm
Height	0.709 in
Width	6 mm
Width	0.236 in
Depth	28 mm

Depth	1.103 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
261-301	ABS	04-HG476174/1-PDA	500	26	2,5
261-301	BV	07436/C0	500	24	0,08-2,5
261-301	CCA	NL5801	500		0,08-2,5
261-301	CSA	18677-45	300	20	26-14
261-301	DNV	E-9215	500	24	2,5
261-301	GL	17295-00HH	500	24	2,5
261-301	KEMA	2110272.02	500	24	0,08-2,5
261-301	KR	HMB05880-EL002	500	24	2,5
261-301	LR	92/20242(E5)	400	24	2,5
261-301	PRS	TE/1718/880590/08	500		0,08-2,5
261-301	RMR	11130002	500	26	2,5
261-301	UR	E45172	300	15	28-14

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected