


Coaxial PCB Connector 82_SMB-50-0-1/111_N

Description

Straight PCB jack

Interface Standards

IEC 60169-10_MIL-STD-348A/311_CECC 22130



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 4 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0008 kg

Environmental Data

Operating temperature -65 °C to 165 °C
2011/65/EU (RoHS) compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Related Documents

Outline drawing DOU-00012686
Catalogue drawing DCA-00012688

Ordering Information

Single package 82_SMB-50-0-1/111_NE
Bulk 100 pcs package 82_SMB-50-0-1/111_NH

Remarks

PCB connector with stand-offs