

# PCT 080807



Sample image

**Order symbol:** PCT 080807

**Product nbr:** 7022561

UL Code: 7032561

UL Name: UL PCT 080807

**Description:** Enclosure. PC


**Remarks:** Clear transparent cover

**EAN:** 6418074003737

**El. number:**

- Finland: 3423526
- Denmark: 8212002597
- Sweden:

**Including:** Base with screws for mounting plate/DIN-rail. cover with PUR gasket and stainless steel cover screws.



Dimensions:	Height	Width	Depth
mm:	80	82	65
inch:	3.15	3.23	2.56

## Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	Clear transparent

## Accessories:

TF 28037	Mounting foot kit (4 pcs). for enclosures:
TM 0808	Back Panel. for enclosures: (56 x 71 x 1)
TH A	Gray plastic hinges (2 pcs)
TRM 0808	DIN-15 Mounting rail. for enclosures: (68 x 15 x 1)

## Rating:

Gasket material: Polyurethane

**Temperatures:**

Temperature °C (short term):: -40 ... 120

Temperature °C (continuous): -40 ... 80

Temperature °F (short term): -40 ... 250

Temperature °F (continuous): -40 ... 175

Ingress protection (EN 60529): IP66; IP67;  
Impact Resistance (EN 62262): IK07; IK08;  
Electrical insulation: Totally insulated  
Halogen free (DIN/VDE 0472, Part 815): 1  
UV resistance: UL 508  
Flammability Rating: UL 746C 5"  
Glow Wire Test (IEC 695-2-1) °C: 960 °C  
NEMA Class

**Certificates:**

SGSFimko\_EURONORD