

## Twist drill, type N with insert 4xD

For universal use up to 1500 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:

Universal use in all material groups up to a strength of 1500 N/mm<sup>2</sup>.

### Execution:

- Twist drill with universal standard geometry and soldered cemented carbide insert (K20)

### Advantage:

- Cemented carbide K20 insert ensures long service life
- polished chipping spaces ensure good chip removal
- cost-effective tool for broad range of applications



<b>Art. no.</b>	<b>11163 260</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11163260
<b>Cutting edge diameter</b>	26 mm
<b>Chip flute length</b>	110 mm
<b>Length</b>	260 mm
<b>DIN</b>	8041
<b>Gross Weight</b>	0.855 kg
<b>Product Group</b>	140

### EAN

4039247030552