

electronic pocket Vernier callipers

IP40

ATORN®

Application

For measuring external, internal, step and depth dimensions.

Version

- ON/OFF
- Zero setting at any position
- mm/inch changeover
- AUTO OFF
- ABS function
- Keeptronic system
- High-contrast display

Advantage

- key lock to prevent unintentional adjustment
- Switched on using the ON button or automatically switched on by calliper movement
- Simple and reliable measurement reading thanks to large and high-contrast display

Delivery

In a case, with battery (1 x 3 V lithium, type CR 2032)



Art. No.	31173 105
Calibration Group	A
Data transmission type	No
IP protection class	IP 40
Min./max. length measuring range	0-150 mm
Length of jaw	40 mm
Length of cross tips	16 mm
Digit height	11 mm
Digit increment	0.01 mm
Depth gauge rod	Flat
Type of locating	With locking screw
Preset function	No
DIN	862

EAN-Code

4050293668544