

Sack truck with push handles and vertical struts

Load capacity up to 250 kg, pneumatic tyres

fetra
Transportgeräte

Execution:

- made of steel tube with sheet steel shovel
- sturdy welded construction
- Shovel can be screwed on and is thus interchangeable
- Wheels with plastic rims and roller bearings
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact- and scratch-resistant

Delivery:

disassembled



Art. no.	50270 319
Brand	FETRA
Manufacturer Part Number	B1116L
Toe plate width	480 mm
Height	1150 mm
Design	With vertical bar
Toe plate depth	300 mm
Load-carrying capacity	250 kg
Width	590 mm
Surface	Powder-coated
Wheel diameter	260 mm
Material	Steel pipe
Material of wheel	Air
Ability to climb stairs	No
Total stop optional	No
Gross Weight	15.000 kg
Product Group	5AB

EAN

4017976211169