

Torque limiter

With 1/4-inch E 6.3 x 25 mm drive and 1/4-inch bit holder

ATORN[®]

Application

For tightening screws in a controlled manner

Version

- Fixed pre-set torque values
- Precise deviation tolerance of +/- 10%
- Tactile indication and clicking noise when torque is reached
- Integrated safety clutch prevents the screw joint from being overtightened
- Coloured outer sleeve with printed torque value - The matching bit insert, which is also colour-coded, can therefore be selected without any problems.
- Carbon steel body with 43-48 HRC, electrically nickel-plated

Advantage

- Optimum protection against overtightening sensitive screw connections
- Easy to handle thanks to the colour coding



Art. no.	52199 206
Tip type	Hexagon
Min./max. torque measuring range	0.6-0.6 Nm
Handle length	53 mm
Error limit (%)	10 %

EAN-Code

4050293668223