

VIP sling chains, quality class 10, 4-stranded

With retractable strands



Application:

For the safe and regulatory-compliant lifting of heavy loads.

Execution:

- CrNiMo stainless steel, special hardening and tempering, quality class 10
- Bright fluorescent pink powder coating (VIP)
- VIP-identification label with integrated chain test gauge, to check the three deposit criteria for sling chains (diameter wear, pitch extension and overload)
- VIP-Cobra safety hook with patented wear marks showing the legal deposit maturity without measuring, marking points for check dimension of the jaw width
- Integrated heat indicator: in the event of inadmissible overheating above 400°C, the colour changes to jet black and small bubbles form
- 4 adjustable chain strands

Advantage:

- Up to 30% higher carrying capacity compared to quality class 8 with the same nominal chain thickness
- No confusion with other quality classes
- Resistant to external mechanical wear and damage
- Longer service life
- VIP-Multi adjustable claw can be attached at any point on the continuous chain strand

Delivery:

1-stranded or longer designs, stronger chain diameter, carrying capacities up to 56 t upon request.



Art. no.	77208 642
Brand	RUD
Manufacturer Part Number	25101000016365
Stop chain design	4 threads
Chain, can be shortened	Yes
Effective length	2 m
Chain diameter	6 mm
Load-carrying capacity at 0-45° tilt angle	3150 kg
Load-carrying capacity at 45-60° tilt angle	2250 kg
EN standard	818-2
Colour	Pink
Gross Weight	12.740 kg
Product Group	775