




Handmikrofone


Handmicrophones



- formstables Kunststoffgehäuse
- 1 Sendetaste "PTT" (TF)
- Reedkontakt (DD65) z.B. für EIN/AUS-Funktion des Funkgerätelautsprechers
- 300 Ohm (omnidirektional)
- 0,28m* PUR-Spiralkabel 4-adrig, 2 Adern geschirmt
- Halter HV7 (DD60); HV7/1 (mit Magnet für DD65)
- l · b · t = 117 · 57,5 · 29mm; 150g
- **optional:** Vorverstärker, kundenspez. Stecker, andere Kabel und zusätzliche Tasten, Lautstärkeregler

- solid plastic housing
- 1 push-to-talk button "PTT" (TF)
- Reed contact (DD65) e.g. on/off-function for radio-loudspeaker
- 300 Ohm (omnidirectional)
- 0,28m* PUR-spiral cable 4-wired, 2 wires shielded
- holder HV7 (DD60); HV7/1 (with magnet for DD65)
- l · w · d = 117 · 57,5 · 29mm; 150g
- **option:** preamplifier, customized connectors, various cables and add. push-buttons, volume control

DD60




* = ungedehnte Spirallänge/unstretched spiral length

Art.-Nr./art.-no.	Bezeichnung/description
2204-005-000-51	DD60/TF/300/HV7/C34
2204-004-000-51	DD65/TF/300/HV7-1/C34

- formstables Metallgehäuse
- 1 Sendetaste "PTT" (TF)
- 1 Sendetaste "PTT" & 1 Ruftaste (TFR)
- 200 Ohm (omnidirektional)
- 0,28m* PUR-Spiralkabel 4-adrig (C34), 6-adrig (C35), 2 Adern geschirmt
- Halter HV5 (extra zu bestellen)
- l = 140mm (TF), 170mm (TFR); Ø = 29mm; 200g (TF), 235g (TFR)
- **optional:** Vorverstärker, kundenspez. Stecker und Tastenbelegungen, Spritzwasserschutz für Mikrofonkapsel (DD112/1)

DD112



* = ungedehnte Spirallänge/unstretched spiral length

HANDMIKROFONE • HANDMICROPHONES

Fortsetzung/Continuation DD112


- solid metal housing
- 1 push-to-talk button "PTT" (TF)
- 1 push-to-talk button "PTT" & 1 call button (TFR)
- 200 Ohm (omnidirectional)
- 0,28m* PUR-spiral cable 4-wired (C34), 6-wired (C35),
2 wires shielded
- holder HV5 (order separately)
- l = 140mm (TF), 170mm (TFR); Ø = 29mm; 200g (TF), 235g (TFR)
- **option:** preamplifier, customized connectors and push button functions
splash proof microphone capsule (DD112/1)

* = ungedehnte Spirallänge/unstretched spiral length

Art.-Nr./art.-no.	Bezeichnung/description
2208-002-000-02	DD112/TF/200/C34
2208-002-000-05	DD112/TF/200/C34
2208-004-000-02	DD112/1/TF/200/C34
2208-013-000-02	DD112/TFR/200/C35
2208-013-000-05	DD112/TFR/200/C35
2208-027-000-05	DD112/1/TFR/200/C35

- formstabiles Metallgehäuse
- 1 Doppeltastschalter für Funk und Mikrofon (TTF)
- Gummischutz für Mikrofonkopf und Sendetastschutz
- 200 Ohm Nahbesprechungsmikrofon (super-direktional,
super-geräuschkompensierend)
- 0,4m* PUR-Spiralkabel 4-adrig, 2 Adern geschirmt
- Halter HV5 (extra zu bestellen)
- l = 180mm; Ø = 29mm; 235g
- **optional:** Vorverstärker, kundenspez. Stecker, andere Kabel

- solid metal housing
- 1 double-push-button for radio and microphone (TTF)
- rubber-protection for microphone head and push-button protection
- 200 Ohm close talking microphone (super-directional,
noise compensating)
- 0,4m* PUR-spiral cable 4-wired, 2 wires shielded
- holder HV5 (order separately)
- l = 180mm; Ø = 29mm; 235g
- **option:** preamplifier, customized connectors, various cables




* = ungedehnte Spirallänge/unstretched spiral length

Art.-Nr./art.-no.	Bezeichnung/description
2102-017-000-03	TM67/11/TTF/200/C72
2102-017-000-05	TM67/11/TTF/200/C72

TM110

- formstabiles Metallgehäuse
- 1 Sendetaste "PTT" (TF)
- 1 Sendetaste "PTT" & 1 Ruftaste (TFR)
- 1 Sendetaste "PTT" & 1 Lautstärke-Potentiometer (TFP)
- 1 Sendetaste "PTT" & 1 Ruftaste & 1 Taste Fernsteuerung (TF2R)
- 1 Doppeltastenschalter für Funk und Mikrofon (TTF)
- 200 Ohm (unidirektional, geräuschkompensierend)
- 0,28m* PUR-Spiralkabel 4-adrig (C34), 6-adrig (C35), 2 Adern geschirmt
- Halter HV5 (extra zu bestellen)
- l = 140mm (TF), 170mm (TFR/TF2R); Ø = 29mm; 200g (TF), 235g (TFR), 280g (TF2R)
- **optional:** Vorverstärker, kundenspez. Stecker, andere Kabel, Montagehalter, Tastenbelegungen, Schwannenhäuse




- solid metal housing
- 1 push-to-talk button "PTT" (TF)
- 1 push-to-talk button "PTT" & 1 call button (TFR)
- 1 push-to-talk button "PTT" & 1 volume control button (TFP)
- 1 push-to-talk button "PTT" & 1 call button 1 push-button for remote control (TF2R)
- 1 double-push-button for radio and microphone (TTF)
- 200 Ohm (unidirectional, noise compensating)
- 0,28m* PUR-spiral cable 4-wired (C34), 6-wired (C35), 2 wires shielded
- holder HV5 (order separately)
- l = 140mm (TF), 170mm (TFR/TF2R); Ø = 29mm; 200g (TF), 235g (TFR), 280g (TF2R)
- **option:** preamplifier, customized connectors, various cables, holders, push button functions, goosenecks

* = ungedehnte Spirallänge/unstretched spiral length

Art.-Nr./art.-no.	Bezeichnung/description
2109-002-000-02	TM110/TF/200/C34
2109-002-000-05	TM110/TF/200/C34
2109-237-000-02	TM110/TF/200/C38-0,4m*
2109-163-000-05	TM110/TF/200/C34 mit PTT-Schutz/with PTT-protection
2109-137-000-02	TM110/TTF/200/C34
2109-032-000-02	TM110/TF/P/200/C34
2109-032-000-05	TM110/TF/P/200/C34
2109-041-000-02	TM110/TFR/200/C35
2109-041-000-05	TM110/TFR/200/C35
2109-187-000-02	TM110/TF2R/200/C35 mit PTT-Schutz/with PTT-protection
2109-164-000-05	TM110/TFR/200/C35 mit PTT-Schutz/with PTT-protection
2109-052-000-02	TM110/TF2R/200/C35
2109-052-000-05	TM110/TF2R/200/C35
2109-181-000-05	TM110/TF/200/Sh.15x300/C14-2,5m

TM210

- formstabiles Metallgehäuse
- 1 Sendetaste "PTT" (TF)
- 1 Sendetaste "PTT" & 1 Ruftaste (TFR)
- 1 Doppeltastschalter für Funk und Mikrofon (TTF)
- 200 Ohm (super-direktional, super-geräuschkompensierend)
- 0,28m* PUR-Spiralkabel 4-adrig (C34), 6-adrig (C35),
2 Adern geschirmt
- Halter HV5 (extra zu bestellen)
- l = 175mm; Ø = 24mm; 200g
- **optional:** Vorverstärker, kundenspez. Stecker, andere Kabel
und Tastenbelegungen



- solid metal housing
- 1 push-to-talk button "PTT" (TF)
- 1 push-to-talk button "PTT" & 1 call button (TFR)
- 1 double-push-button for radio and microphone (TTF)
- 200 Ohm (super-directional, ultra-noise compensating)
- 0,28m* PUR-spiral cable 4-wired (C34), 6-wired (C35),
2 wires shielded
- holder HV5 (order separately)
- l = 175mm; Ø = 24mm; 200g
- **option:** preamplifier, customized connectors, various cables and push button functions


* = ungedehnte Spirallänge/unstretched spiral length

Art.-Nr./art.-no.	Bezeichnung/description
2113-001-000-03	TM210/TF/200/C34
2113-001-000-05	TM210/TF/200/C34
2113-044-000-03	TM210/TTF/200/C34
2113-004-000-03	TM210/TFR/200/C35
2113-004-000-05	TM210/TFR/200/C35

TM214

- formstabiles Metallgehäuse
- 1 Sendetaste "PTT" & 1 Lautstärke-Potentiometer
- 200 Ohm (super-direktional, super-geräuschkompensierend)
- 0,28m* PUR-Spiralkabel 4-adrig (C34), 2 Adern geschirmt
- Halter HV5
- l = 175mm; Ø = 24mm; 200g
- **optional:** Vorverstärker, kundenspez. Stecker und Tastenbelegungen

- solid metal housing
- 1 push-to-talk button "PTT" & 1 volume control button
- 200 Ohm (super-directional, ultra-noise compensating)
- 0,28m* PUR-spiral cable 4-wired (C34), 2 wires shielded
- holder HV5
- l = 175mm; Ø = 24mm; 200g
- **option:** preamplifier, customized connectors and push button functions



* = ungedehnte Spirallänge/unstretched spiral length

Art.-Nr./art.-no.	Bezeichnung/description
2113-008-000-03	TM214/TFP/200/C34
2113-008-000-05	TM214/TFP/200/C34