

KERN EMB 2200-0

Einsteiger-Laborwaage mit enormen Wägeleistungen



Measuring system

Adjustment options:	External calibration
Linearity:	2 g
Readout [d]:	1 g
Recommended adjusting weight:	2 kg (M1)
Reproducibility:	1 g
Resolution:	2200
Stabilisation time:	2,500 s
Warm up time:	10 min
Weighing range [Max]:	2,200 kg
Weighing system:	Strain gauge
Weighing units:	dwt g oz ozt

Display

Display digit height:	1,500 cm
-----------------------	----------

Functions

Suspended weighing:	Hook
---------------------	------

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	5 °C

Power supply

Charging time:	10 h
----------------	------

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	400 h
Operating time (Backlight off):	50 h
Rechargeable battery:	Rchrg. battery optional

Service

Adjustment at the location of installation: 961-247

DAkkS Certificate:	963-127
--------------------	---------

Category

Brand:	KERN
Category:	Balances
Product Group:	School balance

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	226 x 205 x 70 mm
Gross weight:	720 g
Net weight:	515 g
Shipping method:	Parcel service

Construction

Casing material:	Plastic
Dimensions housing (WxDxH):	170 x 240 x 39 mm
Material weighing plate:	Plastic
Weighing surface (d):	150