

Insulation Strippers**15**

- > for stripping thin cables
- > accurate boring to match diameter of wire, precise stripping prism; non-adjustable
- > with opening spring
- > Chrome vanadium electric steel, forged, oil-hardened

15 61 160
MM

Article No.	EAN	↔ mm	Head	Handles	Stripping capacities Ø mm	Δ g
15 51 160	044451	160	MM polished	plastic coated	0,5	101
15 61 160	014843	160	MM polished	plastic coated	0,6	102
15 81 160	015574	160	MM polished	plastic coated	0,8	102

Dismantling Tools**16**
20

- > for stripping all common round cables
- > self-tightening holding lever
- > with adjusting screw for cutting depth adjustment
- > turnable blade for circular and longitudinal cutting
- > spare blade inside the handle
- > secure grip due to soft component material on handle and holding lever to avoid slipping
- > housing: plastic, impact-proof

16 20 165 SB

with knife and hook blade, protective cap included

16 20 16 SB
MM16 20 165 SB
MM

Article No.	EAN	↔ mm	Stripping capacities Ø mm	Δ g
16 20 16 SB	060451	130	MM	4.0 - 16.0
16 20 28 SB	060468	130	MM	8.0 - 28.0
16 20 165 SB	043133	165	MM	8.0 - 28.0

16 29 165	043140	Spare blade 16 20 16 SB / 16 20 28 SB / 16 20 165 SB
------------------	--------	---