

# PW 454009 T



Sample image

**Order symbol:** PW 454009 T

**Product nbr:** 4901804

**Description:** PW Inspection Protection window.

**Remarks:** DB3 lock. Transparent cover

**Including:**

**EAN:** 6418074309730

**El. number:**

- Finland: 3424431
- Denmark:
- Sweden:

Dimensions:	Height	Width	Depth
mm:	452	400	88
inch:	16	14	3.3

Rating:	
Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK09;

**Materials:**

Material:	Polycarbonate
Base colour:	
Cover colour:	
Gasket material:	

**Temperatures:**

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Electrical insulation:	Not insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	NEMA 4, 4X, 12 and 13

**Certificates:**