

tesa® 4329 PV1

Finely crêped paper masking tape.

The product is thin and flexible and therefore suitable for all general masking applications, as well as oven drying applications up to a temperature of 70 °C.

Main Application

The product is resistant to wet sanding. Paints and fillers adhere well to the backing.

The material can be used on painted metal, rubber, glass and chrome parts.

Technical Data

▪ Backing material	slightly-creped paper	▪ Elongation at break	10 %
▪ Total thickness	125 µm	▪ Tensile strength	33 N/cm
▪ Type of adhesive	natural rubber	▪ Temperature resistance	70 °C
▪ Adhesion to steel	2.8 N/cm		

Properties

▪ Hand tearability	●●●●	▪ Sharp colour edge	●●●
▪ Easy to remove	yes	▪ Conformability	●●●
▪ Paint anchorage	●●●●		

Evaluation across relevant tesa® assortment: ●●●● very good ●●● good ●● medium ● low

For latest information on this product please visit <http://l.tesa.com/?ip=04329>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.