




**M8 male receptacle front mount incl. nut**

wires PP 4x0,25 1m

Flange M8 male  
4-pole  
Front mounting  
Mounting nut  
with multi-strand wire

**[Link to Product](#)****Illustration**

# Male



Product may differ from Image

## Form

08563

## Technical Data

Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

## Cables

Cable number	969
No./diameter of wires	4 × 0.25 mm <sup>2</sup>
Wire isolation	PP (br, wh, bl, bk)
Shore hardness outer jacket	70 ± 5D
Outer diameter	approx. 1.25 mm
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

## Commercial data

country of origin	DE
-------------------	----

customs tariff number	85444290
minimum order quantity	1

---