


Wire Connector  
Part No: HE3/600V

SYM.	CHANGES	BY	DATE



Working Temperature: 105° C  
Wire Range: #22 - #14 AWG  
Max: 4#16 w /1#20 Min: 1#18 x/1#20

Voltage: 600V  
Voltage for fixtures and signs: 1000V  
All dimensions in mm unless otherwise stated: 0. = ±0.1mm 00. = ±0.2mm 000. = ±0.2mm

NO.	1	2	3
NAME	MATERIAL	COLOR	INTERNATIONAL APPROVALS:
MAT'L.	UL 94V-2 FLAME-RETARDANT	ORANGE	UL/CSA: # E34181
REMARK	THERMOPLASTIC		
APPROVED BY:	CHECKED BY:	DRAWN BY:	



**HOFFMAN PRODUCTS**

20700 Hubbell Avenue, Oak Park, MI 48237  
Tel: 1-800-645-2014 • Fax: 1-800-908-1295  
Web: www.hoffmanproducts.com

DATE:	TITLE: <b>Wire Connector</b>		
SCALE: <b>FREE</b>	PART NO. <b>HE3/600V</b>		
DRAWING NO. <b>H90509</b>	PART NAME	ISSUE	

HOFFMAN CADFILE