


Key features:

- ❑ 2 Position maintained contact keyswitch
- ❑ Key removes in both positions
- ❑ 4 Disc tumbler mechanism
- ❑ Keyed alike
- ❑ Supplied with 2 keys
- ❑ RoHS Compliant



IMPORTANT: This product is for use in 12Vdc and 24Vdc applications only and should only be installed by a qualified person

Dimensions (mm):



Specification:

Mechanical:

Lock — Bright nickel plated alloy
 Tumbler mechanism — 4 Disc
 Cylinder — Chrome plated
 Keys — Brass – nickel plated
 Panel — 2mm G304 ST/ST

Electrical:

Dielectric strength — 1000V / minute
 Insulation resistance — <500M-Ohms typ.
 Current rating — 2A max @12-24Vdc
 Life — 10,000 make and break cycles
 Circuit — 1 x N/O, 1 x N/C

Circuit form & key index:



For normally open contacts (NO)
 Connect between BLACK & WHITE
 For normally closed contacts (NC)
 Connect between RED & BLUE

Ordering information:

SR09745 2 position keyswitch, maintained contact, 1 gang, SSS, laser etched ON / OFF
 SR09746 2 position keyswitch, maintained contact, NS, SSS, laser etched ON / OFF



Online: cpc.co.uk
 Telephone: 08447 88 00 88
 Fax: 08447 88 00 89