

CARDMASTER ABS 36/31-3



Sample photo

Order symbol: ABS 36/31-3
Product nbr: 7585020
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056801
EI. number:
 Finland: 3438246
 Electric No. 8212016787
 Denmark:
 Electric No. Sweden: 7585020

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	390	316	167	FP 36/31 Front plate (aluminium)
inch:	15.4	12.4	6.6	
Materials:	Material: ABS Base colour: RAL 7035 -light grey Cover colour: Smoked grey Gasket material: EPDM & PUR			
Temperatures:	Temperature °C (short term): -40 ... 80 °C Temperature °C (continuous): -40 ... 60 °C Temperature °F (short term): -40 ... 175 °F Temperature °F (continuous): -40 ... 140 °F			
Accessories:	MP 36/31 Mounting plate			
Rating:	Ingress Protection (EN 60529): IP65 Impact Resistance (EN 62262): IK07 Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): 1 Flammability Rating: UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 3, 3R, 12, 13			
Certificates:	Gost R			

