

Subject: EARPHONE

Model No.: MH300C-1 (28-005)

1. Photo



2. Schematic Diagram



3. General Specification

Dimension	Φ13mm Speaker
Impedance	32±15%Ω at 1KHz
Sensitivity	100±5dB at 1KHz 10mw
Frequency Range	20~20KHz
Rated Power Input	10mW
Max. Power Input	15mW
Plug	φ3.5mm mono ni-plated type
Length of cable	Ø1020 PVC cable 1800±50mm
Packing	1 piece / zip bag ; 50pcs/bag

4. Frequency Response

12/31/2019 15:20

CRY6125RT手机免提耳机传声器测试仪U91

耳机输入

型号: _____ 1kHz灵敏度 耳机: 096.52dB 咪头: _____ dB 串音: _____ dB 滤波器1次
平均灵敏度 → 096.15dB _____ dB _____ dB 无框
电压: 0178 mV 阻抗 0026.6 Ω 电流: _____ uA _____ mV 自动: 免测

120 0 dB 参考值为: 20.0 μPa 扫频速度: 001 ms 快速 扫频模式: 1/24 Oct

