

Eco G9 Capsule

Hi-PIN Eco G9 Capsule 230V 42W SV1
0022844



Product features

- Eco G9 Capsule



PRODUCT OVERVIEW

Product name	Hi-PIN Eco G9 Capsule 230V 42W SV1
Technology	Halogen
Watt (Rated) (W)	42
Lamp shape	Capsule
Type	Eco G9 Capsule
Cap/Base	G9
Lamp finish	Clear
Fixture rating	Open
General application	Hospitality, Museums & Galleries, Retail, Residential & Consumer
ETIM Class	EC000038
Luminous flux (lm)	625
Colour temperature (K)	2800
Light colour	Homelight
CRI (Ra)	100
Wattage (W)	42
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	2000
Product EAN number	5410288228440

DATA TABLE

General data

Product name	Hi-PIN Eco G9 Capsule 230V 42W SV1
Technology	Halogen
Watt (Rated) (W)	42
Lamp shape	Capsule
Type	Eco G9 Capsule
Cap/Base	G9
Lamp finish	Clear
Fixture rating	Open
General application	Hospitality, Museums & Galleries, Retail, Residential & Consumer
ETIM Class	EC000038

Optical data

Eco G9 Capsule

Hi-PIN Eco G9 Capsule 230V 42W SV1

0022844

Luminous flux (lm)	625
Luminous flux (Rated) (lm)	625
Colour temperature (K)	2800
Light colour	Homelight
CRI (Ra)	100
Adjustable chromaticity	N
Lumen maintenance at end of nominal life (%)	80

Electrical data

Wattage (W)	42
Equivalent watt (W)	55
Starting time (max) (s)	0.01
Warm-up time to 60% of full light (max) (s)	Instant full light
Mains voltage (V)	230V
Lamp power factor	1
Control gear required	No
No. Of switching cycles before premature failures	>8000
Transformer required	No
Dimming method	Mains: leading / trailing edge
kWh per 1000 hours burning time	42

Lifetime data

Average life (Nominal) (h)	2000
Average life (Rated) (h)	2000

Physical data

Max. Lamp Diameter (mm) - D	14
Weight (kg)	0.004

Packaging

Single packaging type	Mix(80% carton, 20% plastic)
Product EAN number	5410288228440
Packaging single length / height (cm)	6.8
Packaging single width (cm)	2.4
Packaging single depth (cm)	2.4
DUN14 (inner)	15410288228447
Units per inner package	10
Packaging inner length / height (cm)	13.9
Packaging inner width (cm)	13.2
Packaging inner depth (cm)	2.8
DUN14 (outer)	35410288228441
Units per outer package	100
Packaging outer length / height (cm)	27.0
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	15.0

Eco G9 Capsule

Hi-PIN Eco G9 Capsule 230V 42W SV1

0022844

Safety data

Breakage cleaning instructions	Not applicable
Recommendation for disposal at end of life	Not Applicable
Special purpose lamp	No
Suitable for household illumination	Yes

TECHNICAL DRAWINGS

