

Datasheet



REGIOLUX

Category (ETIM):	Light strip
Type:	ILG LED
Order number:	16175024100
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
Mains voltage:	230V / 50Hz
System performance (W):	48
Luminaire luminous flux (lm):	4800
lm/W:	101
Impact resistance (IK rating):	IK06
Certifications:	IP 20, protection class I, Glow-wire flammability test 850°C, F, MM, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	2.06
Dimensions LxWxDxH (mm):	1420 x 56 x 66
Cable entry KE X/Y (mm):	0 / 0
mounting method:	Surface single mounting, Surface light run mounting, Suspended single mounting
EAN-number:	4020863329915
Commodity code:	94051098

ilia-ILG/1500 LED 4800lm 840 • vw • ED • 16175024100




Lighting technology
Diffuser, opal-direct diffuse distribution
ILG/1500 LED 4800 lm 840



Light strip; Housing made of torsion-resistant profiled sheet steel; with captive rotary catches, the profiling of the upper part forms a cable duct for sheathed cables up to 5 x 1.5 mm² cross section; Housing colour traffic white RAL 9016; open distribution; Electrical connection via 3-pole connection terminal with plug-in contacts.

Dimensions LxWxDxH (mm):	1420 x 56 x 66
Cable entry KE X/Y (mm):	0 / 0
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm):	4800
lm/W:	101
Operating device:	Electronic driver (1 pcs.)
System performance (W):	48
Impact resistance (IK rating):	IK06
Certifications:	IP 20, protection class I, Glow-wire flammability test 850°C, F, MM, Indoor, CE



Regiolux GmbH
Type: ilia-ILG/1500 LED 4800 840 ET vw
Article number: 16175024100
Product deep link: <http://www.regiolux.de/en/article/16175024100>
5 year guarantee after registration on website.