

Folding door cabinet, height 1950 mm

With shelf, load capacity 80 kg per shelf

Execution:

- Stable, welded steel sheet structure with base
- Galvanised shelves, height-adjustable in increments of 17 mm
- Practical, inset-type folding doors with internal pivot pins, doors reinforced by box-type profile on inside, approx. 125° door opening angle
- Locks by means of turning handle with triple-point security cylinder lock, incl. 2 keys

Advantage:

- With the folding-door mechanism, more space is provided; ideal for use in narrow passageways or in tight workplaces
- An even better view into the cabinet since large door surfaces no longer block the way

Delivery:

On request: Load capacity per shelf 100 kg with evenly distributed load, DOM locking system (suitable for HK tool cabinets, HK tool shelves, HK workbenches, HK hinged-door and sliding-door cabinets). Other colours available on request.

Art. no.	50046 432
Brand	PAVOY
Manufacturer Part Number	39393-150-500-7357 16
Door design	Full-sheet panel
Height	1950 mm
Depth	500 mm
Width	1500 mm
Number of shelves	4 PCS
Load-carrying capacity per shelf	80 kg
Number of folder height	5 PCS
Load-carrying capacity	400 kg
With partition wall	No
Lock type	Twist-grip lock with three-point fastening
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Gross Weight	100.000 kg
Product Group	5CB