

## Keyhole saws made of HSS bi-metal

**ATORN®**

### Application

For sawing circular holes in unalloyed steel (up to 700 N/mm<sup>2</sup>), non-ferrous metals, light metals, plastics, plaster, fibre and plywood boards, light-weight building boards and general wood processing.

### Version

- High degree of concentricity
- Solid base plate with improved stability
- Cutting depth maximum 38 mm
- Drill bit can be replaced with other commercially available mounts
- Excludes mounting shank and drill bit; please order separately!
- In individual packages, with information regarding cutting values

### Advantage

- Lateral slots in the body help to remove cut parts
- More even cut, reduced vibration and heat generation and less force required thanks to variable teeth spacing with 4/6 teeth per inch



<b>Art. No.</b>	<b>53841 019</b>
<b>Diameter</b>	19 mm

### EAN-Code

4050293171303