



MASTER TL5 High Output

MASTER TL5 HO 80W/865 SLV/40

This TL5 lamp (tube diameter 16 mm) offers high light output. The TL5 HO lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and color rendering. Application areas vary from offices and industry to schools and retail environments.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Color Designation	
Cap-Base	G5 [G5]		Cool Daylight
Life to 50% Failures Preheat (Nom)	30000 h	Luminous Efficacy (@ Max Lumen, Rated) (Nom)	83 lm/W
Features	na [Not Applicable]	Correlated Color Temperature (Nom)	6500 K
System Description	High Output	Luminous Efficacy (rated) (Nom)	79 lm/W
LSF Preheat 2000 h Rated	99 %	Color Rendering Index (Max)	85
LSF Preheat 4000 h Rated	99 %	Color Rendering Index (Min)	80
LSF Preheat 6000 h Rated	99 %	Color Rendering Index (Nom)	82
LSF Preheat 8000 h Rated	99 %	LLMF 2000 h Rated	96 %
LSF Preheat 16000 h Rated	97 %	LLMF 4000 h Rated	95 %
LSF Preheat 20000 h Rated	84 %	LLMF 6000 h Rated	94 %
		LLMF 8000 h Rated	93 %
		LLMF 12000 h Rated	92 %
		LLMF 16000 h Rated	91 %
		LLMF 20000 h Rated	90 %
Light Technical			
Color Code	865 [CCT of 6500K]		
Luminous Flux (Nom)	6300 lm		
Luminous Flux (Rated) (Nom)	6300 lm		

MASTER TL5 High Output

Operating and Electrical

Power (Nom)	80 W
Lamp Current (Nom)	0.530 A

Temperature

Design Temperature (Nom)	35 °C
--------------------------	-------

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Cap-Base Information	Green Plate
----------------------	-------------

Approval and Application


Energy Efficiency Label (EEL)	A
-------------------------------	---

Mercury (Hg) Content (Nom)	1.4 mg
Energy Consumption kWh/1000 h	88 kWh

Product Data

Full product code	871150071047555
Order product name	MASTER TL5 HO 80W/865 SLV/40
EAN/UPC - Product	8711500710475
Order code	927929586557
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	40
Material Nr. (12NC)	927929586557
Net Weight (Piece)	127.400 g
ILCOS Code	FDH-80/65/1B-L/P-G5-16/1450


Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HO 80W/865 SLV/40	17 mm	1449.0 mm	1456.1 mm	1453.7 mm	1463.2 mm

TL5 HO 80W/865

Photometric data



LDPB_TL5-HO8_865-Spectral power distribution B/W



LDPO_TL5-HO8_865-Spectral power distribution Colour

MASTER TL5 High Output

Lifetime



LDLE_TL5-HO8_0001-Life expectancy diagram

LDLE_TL5-HO8_0002-Life expectancy diagram



LDLM_TL5-HO8_0001-Lumen maintenance diagram

