PHILIPS Lighting



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold[™] MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Chromaticity Coordinate X (Nom)	300
Cap-Base	PGJX28 [PGJX28]	Chromaticity Coordinate Y (Nom)	324
Operating Position	UNIVERSAL [Any or Universal (U)]	Correlated Color Temperature (Nom)	7200 K
Main Application	Entertainment	Luminous Efficacy (rated) (Nom)	69 lm/W
Life to 50% Failures (Nom)	750 h	Color Rendering Index (Nom)	75
System Description	MiniFastFit		
		Operating and Electrical	
Light Technical		Power (Nom)	700 W
Color Code	2	Lamp Current (Nom)	10.2 A
Luminous Flux (Min)	44000 lm	Ignition Supply Voltage (Min)	198 V
Luminous Flux (Nom)	47000 lm		

MSR Gold[™] MiniFastFit (Touring/Stage)

Controls and Dimming		
Dimmable	Yes	
Mechanical and Housing		
Cap-Base Information	PGJX28	
Luminaire Design Requirements		
Bulb Temperature (Max)	950 °C	
Pinch Temperature (Max)	500 ℃	
Product Data		
Full product code	871829122117300	

Order product name	MSR Gold™ 700/2 MiniFastFit 1CT/4	
EAN/UPC - Product	8718291221173	
Order code	928199905115	
Numerator - Quantity Per Pack	1	
Numerator - Packs per outer box	4	
Material Nr. (12NC)	928199905115	
Net Weight (Piece)	0.052 kg	


Dimensional drawing




Product D о L L L с F F F (max) (min) (max) (min) (max) (max) MSR Gold™ 55 mm 57 mm 56 23.2 3.8 112 mm 36.5 36 35.3 700/2 mm mm mm mm mm mm MiniFastFit 1CT/4

MSR GOLD 700/2 MiniFastFit

Photometric data



XDPB_XDMSR_0004-Spectral power distribution B/W



MSR Gold[™] MiniFastFit (Touring/Stage)



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2020, October 15 - data subject to change