

Artikel Nr.: 342032

Pendelleuchte, Filo Sat, schwarz, 220-240V AC/50-60Hz, 3x max. 60,00 W

Technische Daten

Charakteristik

Material	Metall / Aluminium
Farbe	schwarz
Optik	
im Lieferumfang	




Elektrische Daten

Leistung	3x max. 60,00 W
Eingangsspannung	220-240V AC/50-60Hz
Eingangsstrom	
Fassung / Sockel	E27
Anzahl Sockel	3
Netzgerät	
Ansteuerung	dimmbar über optionales Leuchtmittel
Anschlussmöglichkeit	Klemme
Schutzklasse I, II, III	I



Artikel Nr.: 342032

Pendelleuchte, Filo Sat, schwarz, 220-240V AC/50-60Hz, 3x max. 60,00 W



Lichtrichtung

Dreh- und Schwenkbereich	feststehend
Neigungswinkel	
Abstrahlverhalten	
Reflektor / Linse	symmetrisch

Abmessungen und Gewicht

Länge	
Breite	
Höhe	180 mm
Durchmesser	390 mm
Deckenabhängung	1,20 m
Gewicht	2565 g

Sockelmaß


Länge	
Breite	
Höhe	25 mm
Durchmesser	100 mm

Artikel Nr.: 342032

Pendelleuchte, Filo Sat, schwarz, 220-240V AC/50-60Hz, 3x max. 60,00 W

Grenzwerte

Betriebstemperatur	-5°C - +40°C
Lagertemperatur	
IP - Schutzart	IP20

EEL	Die Leuchte ist geeignet für Leuchtmittel der Energieeffizienzklassen A++ bis E
IP20	Schutz gegen das Eindringen von Fremdkörper > 50 mm. Kein Schutz gegen das Eindringen von Wasser.
	Leuchte der Schutzklasse I bei der der Schutz gegen elektrischen Schlag nicht allein auf der Basisisolierung beruht, sondern die eine zusätzliche Sicherheitsvorkehrung derart enthält, dass berührbare leitfähige Teile mit Mitteln zum Anschluss an den Schutzleiter der festen Installation ausgerüstet sind, so dass im Fehlerfall der Basisisolierung berührbare leitfähige Teile nicht aktiv werden können.

Article no.: 342032

Pendant lamp, Filo Sat, black, 220-240V AC/50-60Hz, 3x max. 60,00 W

Technical Data**General Characteristics**

Material	metal / aluminum
Colour	black
Optics	
included in delivery	

**Electrical Characteristics**

Power	3x max. 60,00 W
Input voltage	220-240V AC/50-60Hz
Input current	
Base (standard designation)	E27
Number of bases	3
Power supply unit	
Electronically reversible	dimnable via optional bulb
Connection possibility	clamp
Protection class I, II, III	I



Article no.: 342032

Pendant lamp, Filo Sat, black, 220-240V AC/50-60Hz, 3x max. 60,00 W

Light Direction


Rotating and tilting range	fixed
Angle of inclination	
Radiation direction	
Reflector / lense	symmetrisch

Dimensions & Weight

Length	
Width	
Height	180 mm
Diameter	390 mm
Suspensions from ceiling	1,20 m
Product Weight	2565 g

Base dimensions

Length	
Width	
Height	25 mm
Diameter	100 mm



Article no.: 342032

Pendant lamp, Filo Sat, black, 220-240V AC/50-60Hz, 3x max. 60,00 W

Absolute maximum ratings

Working temperature	-5°C - +40°C
Storage temperature	
IP - Code	IP20

EEL	The luminaire is suitable for lamps of energy efficiency classes A++ to E.
------------	--

IP20	Protection against penetration of foreign objects > 50 mm. No protection against penetration of water.
-------------	--



Lightings of Protection Class I in which the protection against electric shock is not based solely on isolation, but an additional safety measure contains such a way that accessible conductive parts are equipped with means for connection to the protective conductor of the fixed installation, so that in case of failure of the basic insulation exposed conductive parts cannot be active.
