

CD-BO 40X60 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Similar to illustration

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

| | |
|------------|---|
| Type | CD-BO 40X60 8/12 GY |
| Order No. | 2589890000 |
| Version | Cable duct floor duct, 40 mm x 60 mm, 8.00 mm x 12.00 mm, 2000 mm |
| GTIN (EAN) | 4050118600872 |
| Qty. | 24 m |

CD-BO 40X60 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

| | | | |
|------------|----------|-----------------|------------|
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Width | 60 mm | Width (inches) | 2.362 inch |
| Height | 40 mm | Height (inches) | 1.575 inch |
| Net weight | 450 g | | |

General information

| | | | |
|----------------------|---|---------------------------|---------|
| Colour | grey | Cover | Yes |
| Flexible wiring duct | No | Halogen | Yes |
| Material | PVC | Non-tracking | Yes |
| Slit gap | 12 mm | Slit width | 8 mm |
| Type of mounting | when screwed in, With adhesive, Riveted | UL 94 flammability rating | V-0 |
| Usable cross-section | 1,960 mm ² | Version of side panel | slotted |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 6.0 | EC000012 | eClass 6.2 | 27-40-07-03 |
| eClass 9.1 | 27-40-07-03 | | |

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data

[STEP](#)

Data sheet

CD-BO 40X60 8/12 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

