


AS-Interface universal module

EMS/Module/4DI/CCT



1 panel for labelling

**Electrical data**

Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	200

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4
------------------------------	-----------------------------

Inputs

Number of digital inputs	4
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Voltage supply [V]	20...30
Max. total current rating of inputs [mA]	160
Input current High [mA]	> 5
Input current Low [mA]	< 3
Min. switching level high signal [V]	10
Digital inputs protected against short circuits	yes

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals

EMC	EN 50295
-----	----------

AC2032

AS-Interface universal module

EMS/Module/4DI/CCT



AS-i classification									
AS-i profile	S-0.0.F								
AS-i I/O configuration [hex]	0								
AS-i ID code [hex]	0.F								
AS-i certificate pending	yes								
Assignment of the data bits	data bit assignment	D0 I-1	D1 I-2	D2 I-3	D3 I-4				
Mechanical data									
Weight [g]	182								
Type of mounting	AS-i interface to FC and SC lower parts								
Materials	PA 6-GF30; stainless steel (1.4305 / 303)								
Displays / operating elements									
Display	operation	LED, green							
	errors	LED, red							
	function	LED, yellow							
Remarks									
Pack quantity	1 pcs.								
Electrical connection									
cage clamps:									
contact pins to module lower part, FK / PG:									