


# AC3227



## AS-i fibre optic repeater

SmartL25 AS-i FO-Repeater



- 1 plug with cage clamp connection
- 2 panel for labelling
- 3 mounting on DIN rail



Application		
Application	Extension of the AS-i network via fibre optics to max. 3200 m	
Electrical data		
Nominal voltage DC [V]	26.5...31.6	
Max. current consumption from AS-i [mA]	60	
Operating conditions		
Ambient temperature [°C]	-25...70	
Storage temperature [°C]	-30...80	
Max. relative air humidity [%]	90; (non condensing)	
Max. height above sea level [m]	2000	
Protection	IP 20	
Tests / approvals		
EMC	EN 62026-2	
	Ta	-25...70 °C
UL approval	Enclosure type	IP20
	voltage supply	Low Voltage / Limited Energy
	File number UL	E205959



# AC3227



## AS-i fibre optic repeater

SmartL25 AS-i FO-Repeater

Mechanical data		
Weight	[g]	162.5
Type of mounting		mounting on DIN rail
Materials		PA 6.6
Displays / operating elements		
Display	operation	1 x LED, green
Accessories		
Accessories (supplied)		COMBICON connectors
Remarks		
Remarks		An additional AS-i power supply is required for operation.
Pack quantity		1 pcs.
Electrical connection		
Connection		



A+	AS-i +
A-	AS-i -
T1	Link for bus termination
T2	Link for bus termination