

5W LED GU10 Lamp



Specifications

Lamp Style	: Reflector
Lamp Base Type	: GU10
Dimmable	: Not Dimmable
Beam Angle	: 38 Degree
Equivalent Wattage	: 35W
Luminous Flux	: 400lm
Power Rating	: 5W
Supply Voltage	: 220V to 240V, 50Hz
Energy Rating	: A+
Colour Rendering	: ≥80
Life	: 25000 hrs.

Part Number Table

Description	Colour Temperature	LED Colour	Part Number
5W LED GU10 Lamp	3000K	Warm White	PEL00543
	4000K	Cool White	PEL00544
	6000K	Daylight White	PEL00545

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.