

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0191640015](#)  
**Status:** **Active**  
**Overview:** [Perma-Seal Terminals](#)  
**Description:** Perma-Seal Male Quick Disconnect Tab for 18-22 AWG Wire, Tab Size 6.35 x 0.81mm

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR18689  
 UL E79133

**General**

Product Family Quick Disconnects  
 Series [19164](#)  
 Crimp Quality Equipment Yes  
 Insulated Partial  
 Overview [Perma-Seal Terminals](#)  
 Product Name Perma-Seal  
 Type Quick Disconnect  
 UPC 800753113039

**Physical**

Barrel Type Closed  
 Color - Resin Red  
 Gender Male  
 Glow-Wire Capable No  
 Insulation NiAc  
 Lock to Mating Part None  
 Material - Metal Brass  
 Material - Plating Mating Zinc Chromate  
 Material - Plating Termination Zinc Chromate  
 Material - Resin Nylon  
 Net Weight 1.633/g  
 Orientation Straight  
 Packaging Type Bag  
 Plating min - Mating 5.080µm  
 Plating min - Termination 5.080µm  
 Tab Thickness 0.81mm  
 Tab Width 6.35mm  
 Temperature Range - Operating -55° to +125°C  
 Wire Insulation Diameter 3.81mm max.  
 Wire Size AWG 18, 20, 22

**Electrical**


Voltage - Maximum 600V

**Material Info**

Engineering Number SAA-9260

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19164-038



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 ED/61/2018 (27 June  
 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19164 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**