


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0357470110**  
**Status:** **Active**  
**Overview:** VersaBlade Wire-to-Wire Connector System  
**Description:** VersaBlade .070 Male Crimp Terminal, 20-22 AWG, Type B

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-35150-001-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-35182-003-001 (PDF)</a>
<a href="#">Product Specification 351800400-001 (PDF)</a>	<a href="#">Packaging Specification PK-35747-001-001 (PDF)</a>
<a href="#">Product Specification 351800600-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**General**

Product Family	Crimp Terminals
Series	<u>35747</u>
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>VersaBlade Wire-to-Wire Connector System</u>
Product Name	VersaBlade
UPC	800754378505

**Physical**

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.293/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.70mm max.
Wire Size AWG	20, 22
Wire Size mm <sup>2</sup>	N/A

**Material Info**

**Reference - Drawing Numbers**

Crimp Specification	CS-35745-001-001, CS-35745-001-002
Packaging Specification	PK-35747-001-001
Product Specification	351800400-001, 351800600-001, PS-35150-001-001, PS-35182-003-001
Sales Drawing	SD-35747-001

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/61/2018 (27 June  
2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

35747 Series

**Mates With**

35748 Crimp Terminal

**Use With**

35150 VersaBlade Hybrid Receptacle Housing. 35151 VersaBlade Hybrid Plug Housing