


P2665

Pylon Probe

Product Family: Pylon



Mechanical:

Test Center (mil): 125

Test Center (mm): 3.18

Overall Length (mil): 1,290

Overall Length (mm): 32.77

Overall Length Remark: Tip 2W: 1270 mil (32.26 mm)

Full Travel (mil): 230

Full Travel (mm): 5.84

Recommended Travel (mil): 167

Recommended Travel (mm): 4.24

Thermal:

Max Operating Temp (°C): 150

Min Operating Temp (°C): -55

Electrical:

Current Rating (Amps): 15

Average DC Resistance lower than (mOhm): 10

Springs

Force Type - Preload in oz (g) - Rec. Travel in oz (g) -

Spring Material

Standard - 1.50 (43.00) - 3.00 (85.00) - Stainless Steel

Alternate - 2.50 (71.00) - 5.80 (164.00) - Stainless Steel

Body Type

Straight

Pylon Bend

Additional information:

Uses insertion tool RIT-3-0

Materials & Finishes:

Plunger Material: Heat-treated BeCu, Gold plated over hard Nickel

Barrel Material: Phosphor Bronze, Gold plated


Ball Material: Stainless Steel

TIPS:


Tip Materials: BeCu, Gold plated

Tips:


P2665-1C




P2665-1R




P2665-1V



P2665-1W




P2665-2W




Related Products:


PR80-0




PR80-0F




PR80-1




PR80-1F




PR80-2



PR80-2F



PR80-3



PR80-3F

