

Pneumatic ratchet screwdriver MDR 2100

**MANNESMANN
DEMAG**

Application:

For use in confined spaces

Version:

- Thermally insulated soft handle
- Exhaust air duct can be rotated 360°
- With speed control



Art. no.	75061 200
Model	MDR 2100
Suitable for screw	M10
Max. tightening torque	55 Nm
Max. idle speed	220 rpm
Air consumption	4.7 l/s
Tool holding device	1/4-inch external square
Connection thread	NPT 1/4 inch
Inner hose diameter	8 mm
Sound-pressure level	82 dB
Valve design	Lever valve
Length	200 mm
Weight	0.6 kg
With right/left-hand rotation	Yes

EAN-Code

4251757302701

