

# BRUSHLESS DC FAN

# F17FA

## FEATURES

- 17 x 17 x 5 mm miniature fan.
- Proprietary impeller design provides high air flow and quiet operation. (0.01m<sup>3</sup>/min, 5dB(A) at 7000rpm)


RoHS compliant



## APPLICATIONS

- Video equipments
- Information systems
- Telecommunication equipments

## PART NUMBER DESIGNATION



## LIST OF PART NUMBERS

Power supply	Part number
DC3.3 V	F17FA-03MC

※ Verify the above part numbers when placing orders.

# F17FA


## MINIATURE BRUSHLESS DC FAN MOTORS

### STANDARD SPECIFICATIONS

Item	F17FA-03MC
Rated voltage	DC3.3 V
Voltage range	3.1 ~ 3.5 V
Rated current	0.07 A
Rotating speed	7000 min <sup>-1</sup>
Air flow	0.01 m <sup>3</sup> /min
Static pressure	6 Pa
Noise	5 dB (A)
Use environment	0 ~ +60 °C (35 ~ 85 %RH)
Storage environment	-10 ~ +70 °C (35 ~ 85 %RH)
Net weight	Approx. 1.5 g

※The specifications above are typical values measured on the conditions of no-loading running with rated voltage in the circumstances of 25 °C ± 2 °C, 35~ 85 %RH. Please contact us if you would liketo check the specifications in different circumstances.

### AIR FLOW PERFORMANCE CURVES



※ Data in our measuring instrument

### OUTLINE DIMENSIONS

(Unit: mm)

