

[Products](#) [Multimeter](#) [Digital handheld multimeter](#) [PeakTech® 3320](#)

PeakTech® 3320 PROD-ID: P 3320

[BACK](#)

Digital Multimeter ~ 6.000 Counts ~ 600V AC/DC ~ 10A AC/DC with TrueRMS

Multimeter designed as per highest safety standard CAT III 600 V/CAT II 1000 V featuring modern style, integrated protection frame. The 3 5/6 digit LCD-display (max. 6000) with function symbols, 61 segment analogue bargraph and backlight guarantee exact data acquisition. The True RMS AC voltage and current readings, non-contact voltage detector are most important features of this excellent multimeter.

- 3 5/6 digit, 20 mm LCD-display, max. 6000
- Continuity- and diode test
- Data Hold, MIN/MAX Hold
- Auto- and manual range selection
- Auto power off
- Safety: EN 61010-1; CAT III 600 V/CAT II 1000 V
- Accessories: carrying case, test leads, type K-temperature probe, temp.-adaptor, battery and operation manual



MANUAL

[PeakTech_3320_DE_EN_FR_03-2019F.pdf \(648.3 kB\)](#)

PICTURES

[3320_Accessories.jpg \(497.9 kB\)](#)

[3320_Front.jpg \(364.5 kB\)](#)

[3320_L.jpg \(386.6 kB\)](#)

[3320_R.jpg \(423.6 kB\)](#)

DCV	600 mV/6/60/600 V - 0,1 mV; $\pm 1,2\%$ + 2 dgt.
ACV	6/60/600 V - 1 mV; $\pm 1,5\%$ + 10 dgt.
DCA	6/10 A - 1 mA; $\pm 2,5\%$ + 5 dgt.
ACA	6/10 A - 1 mA; $\pm 3,0\%$ + 5 dgt.
Ohm	600 Ω /6/60/600 k Ω /6/60 M Ω - 0,1 Ω ; $\pm 1,0\%$ + 2 dgt.
Capacitance	40/400 nF/4/40/400/4000 μ F - 10 pF; $\pm 5,0\%$ + 5 dgt.
Frequency	10/100 Hz/1/10/100 kHz/1/10 MHz - 1 mHz; $\pm 1,2\%$ + 3 dgt.
Temperature	-20 ... +760 °C - 1 °C; $\pm 3,0\%$
Operation voltage	9 V-battery
Dimensions (WxHxD)	70 x 150 x 48 mm
Weight	260 g
EAN-13	4250569400827

