

**TECHNICAL SPECIFICATIONS**

**D-Sub Hood:**


Material: UL 94 V-0 Plastic Material  
 Plating: Nickel over Copper  
 Operating Temperature: -55°C to +110°C  
 Cable Entry: Side Entry  
 Thumbscrews: UNC 4-40 (Standard)  
 Cable O.D: Up to 11,5mm

**Female D-Sub Solder Cup:**

Insulator: PBT, Black, UL94 V-0  
 Shell: Steel, Tin Plated  
 Contact pins: Copper Alloy  
 Stamped & Formed Pins: Class 3, 100 inserts min.  
 Machined Contact Pins: Class 1, 500 inserts min.  
 Contact Plating: Selective Gold over Nickel  
 Operating Temperature: -55°C to +105°C  
 Withstanding voltage: 1000V for 1 minute  
 Insulator resistance: 1000MΩ min.

**Features:**

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D Connector
- Strain relief inserts ensure a secure termination
- Re-openable
- Recyclable



Size D45PK-M	Dim A	Dim B	Dim C
9-way	31,0	36,3	15,0
15-way	39,5	40,3	15,0
25-way	53,2	40,3	15,0
37-way	69,7	40,3	15,0

**Ordering information - Black Insulator:**

Size:	P/N - Kitted:	Class 3 - 100 inserts min.
9-way	6355-0009-11	D45PK-M-09-DBS-K
15-way	6355-0009-12	D45PK-M-15-DBS-K
25-way	6355-0009-13	D45PK-M-25-DBS-K
37-way	6355-0009-14	D45PK-M-37-DBS-K

Size:	P/N - Kitted:	Class 1 - 500 inserts min.
9-way	6355-0010-11	D45PK-M-09-DMS-K
15-way	6355-0010-12	D45PK-M-15-DMS-K
25-way	6355-0010-13	D45PK-M-25-DMS-K
37-way	6355-0010-14	D45PK-M-37-DMS-K

**Ordering information - White Insulator:**

Size:	P/N - Kitted:	Class 3 - 100 inserts min.
9-way	6355-8009-11	D45PK-M-09-DBS-W-K
15-way	6355-8009-12	D45PK-M-15-DBS-W-K
25-way	6355-8009-13	D45PK-M-25-DBS-W-K
37-way	6355-8009-14	D45PK-M-37-DBS-W-K

Size:	P/N - Kitted:	Class 1 - 500 inserts min.
9-way	6355-8010-11	D45PK-M-09-DMS-W-K
15-way	6355-8010-12	D45PK-M-15-DMS-W-K
25-way	6355-8010-13	D45PK-M-25-DMS-W-K
37-way	6355-8010-14	D45PK-M-37-DMS-W-K

