

Han-Eco Mod.24-C-f. HBM/HSM-cord



Part number	19 41 024 5404
Specification	Han-Eco Mod.24-C-f. HBM/HSM-cord
HARTING eCatalogue	https://b2b.harting.com/19410245404

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Eco® Modular
Type of hood/housing	Protection cover
Description of hood/housing	for bulkhead mounted housings for surface mounted housings for cable to cable housing With fixing cord

Version

Locking type	Double locking lever
Size	24 B

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Specifications	IEC 61984 EN 45545-2 R22: HL1, HL2, HL3
----------------	--



Pushing Performance

Specifications and approvals

	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	1
Net weight	70.2 g
Country of origin	Germany
Customs tariff number	85389099