

ARCA 203015



Sample photo

Order symbol: ARCA 203015
Product nbr: 8120020
Description: Cabinet, PC
Remarks: Grey cover, 1-point locking, hinges on the short side

EAN: 6418074079312
EI. number:
 Finland: 3423117
 Denmark: 8212091184
 Sweden: 2500109
 Norway:

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		200	300	150	Ingress Protection (EN 60529): IP 66
inch:		7.9	11.8	5.9	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 960
Gasket material:		PUR			Certificates:
					SGS Fimko
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 3020		Mounting plate			
MPP ARCA 3020		Mounting plate perforated			
MPX ARCA 3020		Mounting plate			
DRS ARCA 203015		DIN rail frame set			
IDS ARCA 2030		Inner door set			
PMK ARCA 30		Pole mounting kit			

