


# SMART

## BENEFITS

- **Product variants: rewirable and non-rewirable**
- **Overvoltage protection**
- **Easy to mount using screw holes**
- **Practical automatic cable rewind**
- **Robust design**

## SMART

#	
<b>Radio SMART 3x earthing contact 433 MHz</b>   Power strip with integrated radio remote switch, 10A/230V~	
381.800	IP20   Single-pole switching with indicator LED, manually switchable   433.92 MHz, unidirectional, radio range 30 m outdoors   Switchable using remote control or using the app (trained to Wi-Fi SMART Adapter on p. 57)
<b>USB SMART 3x earthing contact</b>   Power strip with integrated 2-way USB charger, 16A/230V~	
381.801	White   IP20   Total charging current for USB charger: max. 3.1 A/5 V



	<b>Dimensions (W x H x D):</b> see table x 56 x 41 mm	:
	<b>Profile:</b> plastic	

**SMART**

#							
---	--	--	--	--	--	--	--

**Supply cable: 5.0m H05VV-F 3G 1.50mm<sup>2</sup> with moulded right-angled plug with earthing contact**

381.152K	6			•	•	350mm	black
381.252K	6			•	•	350mm	white
381.149K	6				•	350mm	black
381.249K	6				•	350mm	white
387.172	3					188mm	black
388.172	3				•	188mm	black
387.272	3					188mm	white
388.272	3				•	188mm	white

**Supply cable: 3.0m H05VV-F 3G 1.50mm<sup>2</sup> with moulded right-angled plug with earthing contact**

381.151K	6			•	•	350mm	black
381.251K	6			•	•	350mm	white
381.148K	6				•	350mm	black
381.248K	6				•	350mm	white
387.171	3					188mm	black
388.171	3				•	188mm	black
387.271	3					188mm	white
388.271	3				•	188mm	white
388.471	3				•	188mm	brown
388.371	3				•	188mm	red
381.2507K		6	•	•	•	350mm	black
381.2512K		6	•	•	•	350mm	white

**Supply cable: 1.5m H05VV-F 3G 1.50mm<sup>2</sup> with moulded right-angled plug with earthing contact**

381.150K	6			•	•	350mm	black
381.250K	6			•	•	350mm	white
381.450K	6			•	•	350mm	brown
381.2501K	6		•	•		390mm	white
381.147K	6				•	350mm	black
381.247K	6				•	350mm	white
381.130K	4			•	•	290mm	black
381.230K	4			•	•	290mm	white
381.121K	4				•	290mm	black
381.221K	4				•	290mm	white
387.170	3					188mm	black
388.170	3				•	188mm	black
387.270	3					188mm	white
388.270	3				•	188mm	white

**Without supply cable**

381.246K	6				•	350mm	white
381.223K	4				•	290mm	white
385.170	3				•	188mm	black
385.270	3				•	188mm	white



381.248K



388.171



388.271



388.471



388.371



381.2512K



381.250K



381.2501K



381.230K



381.221K