



Sample photo

**Order symbol:** PC F 65 T  
**Product nbr:** 8724011  
**Description:** Enclosure, PC  
**Remarks:** Transparent cover

**EAN:** 6418074002181  
**EI. number:**  
 Finland 3423513  
 Denmark 8212001624  
 Italy 7202040  
 Sweden 2536850

**Including:** Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		L	W	H	Rating:		
mm:		230	80	65	<b>Ingress Protection (EN 60529):</b> IP 66/67		
inch:		9.1	3.1	2.6	<b>Impact Resistance (EN 50102):</b> IK 08		
Materials:						<b>Electrical insulation:</b> Totally insulated	
<b>Material:</b>		PC				<b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes	
<b>Base colour:</b>		RAL 7035				<b>UV resistance:</b> UL 508	
<b>Cover colour:</b>		Clear transparent				<b>Flammability Rating (UL 746 C 5):</b> UL 94 5V	
<b>Cover screws material:</b>		Polyamide				<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960	
<b>Cover screws colour:</b>		Grey				<b>NEMA Class:</b> NEMA 1, 4X, 6, 6P, 12, 13	
<b>Gasket material:</b>		Polyurethane				Certificates:	
Temperatures:						Germanischer Lloyd (GL)	
<b>Short term:</b>		-40 ... 120 °C				Underwriters Laboratories	
<b>Continuous:</b>		-40 ... 80 °C				Canadian Standards Association	
<b>Short term:</b>		-40 ... 250 °F				Fimko	
<b>Continuous:</b>		-40 ... 175 °F				Europe EN 50298 1998	
Accessories:						UL Canada	
F-MP		Mounting plate				Gost R	
FM-3		DIN-35 Mounting rail					
FP 22040		Mounting foot kit (2 pcs)					

