

**MATERIAL**

Anodised aluminium oval cross section bar, sandblasted and satin finish.


**STANDARD EXECUTIONS**

Threaded blind holes.

- **RHBG-11:** natural colour.
- **RHBG-14:** black colour.

**SPECIAL EXECUTIONS ON REQUEST**

- Different lengths.
- Surfaces with different finishes.



| Code           | Code           | f   | L   | d   | p  | l  | B  | h  | ⚖️   |
|----------------|----------------|-----|-----|-----|----|----|----|----|------|
| RHBG-30.350.11 | RHBG-30.350.14 | 350 | 377 | M8  | 10 | 31 | 20 | 60 | 525  |
| RHBG-30.400.11 | RHBG-30.400.14 | 400 | 427 | M8  | 10 | 31 | 20 | 60 | 525  |
| RHBG-30.450.11 | RHBG-30.450.14 | 450 | 477 | M8  | 10 | 31 | 20 | 60 | 594  |
| RHBG-30.500.11 | RHBG-30.500.14 | 500 | 527 | M8  | 10 | 31 | 20 | 60 | 594  |
| RHBG-35.400.11 | RHBG-35.400.14 | 400 | 480 | M8  | 10 | 35 | 25 | 62 | 780  |
| RHBG-35.600.11 | RHBG-35.600.14 | 600 | 680 | M8  | 10 | 35 | 25 | 62 | 1164 |
| RHBG-35.800.11 | RHBG-35.800.14 | 800 | 880 | M8  | 10 | 35 | 25 | 62 | 1533 |
| RHBG-40.500.11 | RHBG-40.500.14 | 500 | 540 | M10 | 15 | 41 | 30 | 80 | 1512 |
| RHBG-40.600.11 | RHBG-40.600.14 | 600 | 640 | M10 | 15 | 41 | 30 | 80 | 1512 |
| RHBG-40.700.11 | RHBG-40.700.14 | 700 | 740 | M10 | 15 | 41 | 30 | 80 | 1782 |
| RHBG-40.800.11 | RHBG-40.800.14 | 800 | 840 | M10 | 15 | 41 | 30 | 80 | 1782 |