

**2755 / 2755B / GH275  
GH435 / GH755  
GH810 (-6 to -10)**

**Nipples without  
wire trap**

**Nippel ohne  
Ausreiß-  
sicherung**



**Nipples sans  
gorge pour  
nappes**

**Nipples senza  
protezione da  
strappo**

**Manguitos  
roscados sin  
seguro de  
arranque**

2755(B) / GH275 / GH435 / GH810 (-6 to -10)

GH755



**FHB (6000 psi)**

**SAE Flange Code 62, 90° Elbow  
Flansch-Code 62, 90° Krümmer  
Bride code 62, coude 90°  
Flangia codice 62 a 90°  
Brida-código 62 acodado a 90°**

Part Number Skive Steel	Part Number Skive Stainless Steel	Part Number TTC Steel	Part Number TTC Stainless Steel	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
GC8856-8*		1T8FHB8**			1/2"		12	-8	83,5	50,5	44,7	9,0	31,8		
GC8856-12-8*		1T12FHB8**			3/4"		12	-8	83,5	50,5	78,0	9,0	41,3		
GC8856-8-10* <sup>1</sup>		1T8FHB10**			1/2"		16	-10	87,5	50,9	44,7	12,0	31,8		
GC8856-12-10*		1T12FHB10**			3/4"		16	-10	92,5	56,5	53,5	12,0	41,3		
GC8856-12*		1T12FHB12**			3/4"		19	-12	110,5	74,5	68,0	15,0	41,3		
GC8856-16-12*		1T16FHB12**			1"		19	-12	117,5	80,5	78,5	15,0	47,6		
GC8856-16*		1T16FHB16**			1"		25	-16	118,5	78,0	76,0	20,0	47,6		
GC8856-20-16*		1T20FHB16**			1 1/4"		25	-16	118,5	78,5	81,0	20,0	54,0		

<sup>1</sup> Assembly with full flange is not possible, use split flanges.

<sup>1</sup> Zusammenbau mit Vollflansch ist nicht möglich, benutze Halbflansche.



<sup>1</sup> Embouts où la pleine-bride n'est pas possible, à assembler avec demi bride.

<sup>1</sup> L'assemblaggio con la flangia completa non è possibile, usare la semi-flangia.

<sup>1</sup> No es posible el Montaje con bridas enteras, utilizar medias bridas.

2755(B) / GH275 / GH435 / GH810 (-6 to -10)

GH755



**BF**

**BSP Female Swivel for cone 60°  
BSP-Dichtkopf für Konus 60°  
Globeseal BSP, cone 60°  
Femmina girevole gas per maschio metrico 60°  
Hembra loca BSP para macho con cone de 60°**

Part Number Skive Steel	Part Number Skive Stainless Steel	Part Number TTC Steel	Part Number TTC Stainless Steel	Thread T	Flange	Tube O.D. mm	Hose ND	Hose Size	A mm	D mm	H mm	E mm	K Ø mm	HEX [1]	HEX [2]
41.420-6-6*		1T6BF6**		G 3/8"			10	-6	50,0	20,5		6,5	22		
41.420-8-8*		1T8BF8**		G 1/2"			12	-8	55,5	22,5		9,0	27		
41.420-12-8*		1T12BF8**		G 3/4"			12	-8	56,5	23,5		9,0	32		
41.420-10-10*		1T10BF10**		G 5/8"			16	-10	60,0	23,5		12,0	27		
41.420-12-12*		1T12BF12**		G 3/4"			19	-12	60,5	23,5		15,0	32		
41.420-16-16*		1T16BF16**		G 1"			25	-16	67,0	26,5		20,0	41		

\* Sockets must be ordered separately.

\* Fassungen müssen separat bestellt werden.

\* Les jupes doivent être commandées sêp.

\* Le boccole devono essere ordinate sêp.

\* Los manguitos tienen que pedirse por separado.

\*\* Part numbers include sockets.

\*\* Teil-Nr. beinhaltet Fassang.

\*\* L'embout-Nr. avec la jupe.

\*\* Part Number include la boccola.

\*\* Los números de parte incluyen los manguitos.