

ARCA 705030

FIBOX
Enclosing innovations



Sample image

Order symbol: ARCA 705030

Product nbr: 8120017

Description: Cabinet, PC


Remarks: Grey cover, 2-point locking, hinges on the long side

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate, 3mm double bit lock(s) with key, 5 versions with swinghandle 2-point locking system, Door guide included.

EAN: 6418074079282

El. number:

- Finland: 3423112
- Denmark: 8212091155
- Sweden: 2500120



Dimensions:	Height	Width	Depth
mm:	700	500	300
inch:	27.56	19.69	12.2

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover colour:	RAL 7035 -light grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120
Temperature °C (continuous):	-40 ... 80
Temperature °F (short term):	-40 ... 250
Temperature °F (continuous):	-40 ... 175

Accessories:

SBK ARCA 50	Support bar kit (435 x 40 x 30)
MPX ARCA 7050	Mounting plate (630x430 mm) (630 x 430 x 5)
IDS ARCA 7050	Inner door set (685 x 485 x 35)
DSP ARCA RM	Door stopper ARCA, right, midsize 5070-8060
RCS ARCA 7050	Rain canopy set for size 7050 (20 x 500 x 30)
MPP ARCA 7050	Mounting plate perforated (630x430x2 mm - 26x11 mm) (630 x 430 x 2)
SBK ARCA 70	Support bar kit (615 x 50 x 30)
DSP ARCA LM	Door stopper ARCA, left, midsize 5070-8060
DRS ARCA 705030	DIN rail frame set (685 x 485 x 35)
MPS ARCA 7050	Mounting plate (630x430x2 mm) (630 x 430 x 2)
MPMP ARCA 7050	Mounting plate multiperforated (630x430x2 mm - ø3.6 mm) (630 x 430 x 2)
PMK ARCA 50	PoleMounting kit, for pole ø100-300mm (485 x 385 x 35)

Rating:

Ingress protection (EN 60529):	IP66;
Impact Resistance (EN 62262):	IK10;
Electrical insulation:	Totally insulated
Halogen free (DIN/VDE 0472, Part 815):	1
UV resistance:	UL 508
Flammability Rating:	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C:	960 °C
NEMA Class	NEMA 1, 4, 4X, 12 and 13

Certificates:

Certificate FI 40467